


REVISIONS 変更					
P	LTR	DESCRIPTION	ECN	DATE	DWN APVD
	C1	ECR-19-015554		07OCT2019	SE PKS



注記 ;

1.適用ハウジング : X-316293-X

2.一般公差 ; 10 ≧ : ±0.2
> 10 : ±0.25

NOTES;

1.APPLICABLE HSG : X-316293-X

2.TOLERANCES ; 10 ≧ : ±0.2
> 10 : ±0.25

△3 THIS PRODUCT IS SPLICE FREE VERSION

△3	T	0.76~2.86 mm ² (AWG#18~#13)	316292-5
	L	0.76~2.6 mm ² (AWG#18~#13)	316292-2
	L	0.76~2.6 mm ² (AWG#18~#13)	316292-1
ID マーク ID MARK		抱合電線断面積 WIRE RANGE	型番 P/N
WIRE RANGE 抱合電線断面積		表参照 SEE TABLE	INSULATION DIA 被覆外径 1.6~4.0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.SAKAI	07NOV2011	TE Connectivity	
		CHK M.HARASAWA	07NOV2011		
		APVD N.YAMASAKI	07NOV2011	NAME 名称	
		PRODUCT SPEC 製品規格	108-5494	3.2 CLUSTER REC. L, T TYPE	
		APPLICATION SPEC 取付適用規格	114-5215		
MATERIAL 材料 磷青銅 PHOS BRO		FINISH 仕上 錫めっき TIN PLATED	WEIGHT 0	SIZE A3	CAGE CODE 00779
				DRAWING NO 番号 C-316292	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 尺度 5:1	SHEET 1 OF 1	REV C1