





RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.



SCHEMATIC



PCB LAYOUT



Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.3±0.1mm
Storage Temperature	- 30° C to85° C

Packaging:
Bulk packaging of 1,000 pieces

Mechanical

Actuation Force	Operation Force (gf)	H	Height mm
		43	4.3
L	130±50	50	5.0
M	160±50	70	7.0
H	200±50	73	7.3
K	260±50	95	9.5

X. ±0.50	X.° ±2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD
.X ±0.30	.X° ±1°		
.XX ±0.10	.XX° ±0.5°	MAT'L	PART NO. YTS 645 S X X
.XXX ±0.05			TITLE: TACTILE SWITCH (thro hole)
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH	APPD: ROGER
		Q'TY	CHKD: ROC
			DWG NO. : YTS 645 S X X
			DR: BILLY WANG 2020/08/21
			  SCALE SHEET REV. 1/1 1/1 A1