





RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB layout

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	100Ω min.
Contact resistance	100mΩ max.initial
Dielectric Strength	250 V AC(1mn)
Travel	0.35±0.15mm
Storage Temperature	- 30° C to 85° C

E	STEM	Silicone	1	Black
D	COVER	Stainless Steel	1	Clean
C	HOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	Brass	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

Actuation Force	Operating Force (gf)	Height mm
YTS1C0191ABG00	180±30	2.5
YTS1C0192ABG00	250±50	2.5
YTS1C0193ABG00	350±50	2.5

X. ±0.50	X.° ±2°	UNITS mm
.X ±0.20	.X° ±1°	
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD
Email at info@yiyuanswitches.com

FINISH
Q'TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS1C019

TITLE:
TACTILE SWITCH 4*6mm

APPD: ROGER

CHKD: ROC

DR: BILLY WANG 2020/08/21

DWG NO.:
YTS1C019

SCALE	SHEET	REV.
1/1	1/1	A1

Packaging:
Reel of 3,000 pieces.