




1	2	3	4	5	6	7	8																																																																																				
A					■ SPECIFICATIONS ○ Voltage rating:250V AC/DC ○ Current rating: 2A, AC/DC ○ Withstanding Voltage:800VAC/minute ○ Insulation resistance:1,000MΩ min ○ Temperature range:−40℃to+105℃ ○ Contact resistance:20mΩ max ■ WAFER ○ Part No:CS-1125R-03A 色粉0010 ○ Poles:2-16 ○ Material:Nylon 66 UL 94V-2, 红色 0010 ○ Contact: H65 ○ Contact Plating: Tin ○ Q'TY: 1000 pcs/Tape&reel																																																																																						
B	Recommend PCB Layout																																																																																										
C																																																																																											
D					<table><tr><th rowspan="2">Poles</th><th rowspan="2">PART NO</th><th colspan="3">DIMENSION (mm)</th></tr><tr><th>A</th><th>B</th><th>C</th></tr><tr><td>2</td><td>CS-1125R-02A</td><td>2.00</td><td>6.00</td><td>5.00</td></tr><tr><td>3</td><td>CS-1125R-03A</td><td>4.00</td><td>8.00</td><td>7.00</td></tr><tr><td>4</td><td>CS-1125R-04A</td><td>6.00</td><td>10.00</td><td>9.00</td></tr><tr><td>5</td><td>CS-1125R-05A</td><td>8.00</td><td>12.00</td><td>11.00</td></tr><tr><td>6</td><td>CS-1125R-06A</td><td>10.00</td><td>14.00</td><td>13.00</td></tr><tr><td>7</td><td>CS-1125R-07A</td><td>12.00</td><td>16.00</td><td>15.00</td></tr><tr><td>8</td><td>CS-1125R-08A</td><td>14.00</td><td>18.00</td><td>17.00</td></tr><tr><td>9</td><td>CS-1125R-09A</td><td>16.00</td><td>20.00</td><td>19.00</td></tr><tr><td>10</td><td>CS-1125R-10A</td><td>18.00</td><td>22.00</td><td>21.00</td></tr><tr><td>11</td><td>CS-1125R-11A</td><td>20.00</td><td>24.00</td><td>23.00</td></tr><tr><td>12</td><td>CS-1125R-12A</td><td>22.00</td><td>26.00</td><td>25.00</td></tr><tr><td>13</td><td>CS-1125R-13A</td><td>24.00</td><td>28.00</td><td>27.00</td></tr><tr><td>14</td><td>CS-1125R-14A</td><td>26.00</td><td>30.00</td><td>29.00</td></tr><tr><td>15</td><td>CS-1125R-15A</td><td>28.00</td><td>32.00</td><td>31.00</td></tr><tr><td>16</td><td>CS-1125R-16A</td><td>30.00</td><td>34.00</td><td>33.00</td></tr></table>				Poles	PART NO	DIMENSION (mm)			A	B	C	2	CS-1125R-02A	2.00	6.00	5.00	3	CS-1125R-03A	4.00	8.00	7.00	4	CS-1125R-04A	6.00	10.00	9.00	5	CS-1125R-05A	8.00	12.00	11.00	6	CS-1125R-06A	10.00	14.00	13.00	7	CS-1125R-07A	12.00	16.00	15.00	8	CS-1125R-08A	14.00	18.00	17.00	9	CS-1125R-09A	16.00	20.00	19.00	10	CS-1125R-10A	18.00	22.00	21.00	11	CS-1125R-11A	20.00	24.00	23.00	12	CS-1125R-12A	22.00	26.00	25.00	13	CS-1125R-13A	24.00	28.00	27.00	14	CS-1125R-14A	26.00	30.00	29.00	15	CS-1125R-15A	28.00	32.00	31.00	16	CS-1125R-16A	30.00	34.00	33.00
Poles	PART NO	DIMENSION (mm)																																																																																									
		A	B	C																																																																																							
2	CS-1125R-02A	2.00	6.00	5.00																																																																																							
3	CS-1125R-03A	4.00	8.00	7.00																																																																																							
4	CS-1125R-04A	6.00	10.00	9.00																																																																																							
5	CS-1125R-05A	8.00	12.00	11.00																																																																																							
6	CS-1125R-06A	10.00	14.00	13.00																																																																																							
7	CS-1125R-07A	12.00	16.00	15.00																																																																																							
8	CS-1125R-08A	14.00	18.00	17.00																																																																																							
9	CS-1125R-09A	16.00	20.00	19.00																																																																																							
10	CS-1125R-10A	18.00	22.00	21.00																																																																																							
11	CS-1125R-11A	20.00	24.00	23.00																																																																																							
12	CS-1125R-12A	22.00	26.00	25.00																																																																																							
13	CS-1125R-13A	24.00	28.00	27.00																																																																																							
14	CS-1125R-14A	26.00	30.00	29.00																																																																																							
15	CS-1125R-15A	28.00	32.00	31.00																																																																																							
16	CS-1125R-16A	30.00	34.00	33.00																																																																																							
E	本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.				CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO., LTD.																																																																																						
1	2	3	4	5	6	7	8																																																																																				
类别		WAFER	品名	CS-1125R-03A 色粉0010		材料	单位	mm	SHEET 1 OF 1																																																																																		
版本		A/0	设计	李文畅		颜色	比例	1:1		修改内容	修改日期																																																																																
制定部门		工程课	绘制	李文畅		画法		数量																																																																																			
工程图号		CST-1125R	审核	姚培柱																																																																																							
制定日期		2017-10-18	核准	周中湖				±0.05																																																																																			
1		2	3	4	5	6	7	8																																																																																			

ROHS 2.0