



PIN针规格

SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 2A, AC/DC
- Withstanding Voltage: 800VAC/minute
- Insulation resistance: 1,000MΩmin
- Temperature range: -40°C to +105°C
- Contact resistance: 20mΩmax
- Salt Spray: 12H (5±1% solution at 35±2°C)
- Resistance to Soldering Heat: 245°C ±5°C
- Terminal/Housing Retention Force: 1.0kgf min

WAFER

- Part No: CS-1125-03N2K
- Poles: 2-16
- Material: Nylon 66 UL 94V-0
- Contact: H65
- Contact Plating: Tin
- Q'TY: 1000 pcs/Tape & reel

RoHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	WAFER	品名	CS-1125-03N2K	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
版本	A/1	设计	李文畅	X.X	±0.30	颜色		比例	1:1	①	修改内容	修改日期
制定部门	工程课	绘制	李文畅	X.XX	±0.20	画法	⌀	数量		①		
工程图号	CS-1125	审核	姚培柱	X.XXX	±0.10	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEECTRONICS CO.,LTD.				②		
制定日期	2022-5-31	核准	周中湖	X.XXXX	±0.05					③		