



客户编码			发行日期	2023/3/5																					
客户物料编码			客户规格型号	4*6-5.6MH-0.06线 长脚黑色UL																					
样如物料编码	XR4*6-562K-L		样如规格型号	XR4*6-562K-L																					
送样数量	0PCS		送样日期	2023/3/5																					
外观尺寸 mm			点胶	<table border="1"> <tr> <td>A</td> <td>6.0 MAX</td> <td>E</td> <td>2.0±0.5</td> </tr> <tr> <td>B</td> <td>8.5 MAX</td> <td></td> <td></td> </tr> <tr> <td>C</td> <td>0.5±0.1</td> <td></td> <td></td> </tr> <tr> <td>D</td> <td>15.0±2.0</td> <td></td> <td></td> </tr> <tr> <td>标识</td> <td colspan="3"></td> </tr> </table>	A	6.0 MAX	E	2.0±0.5	B	8.5 MAX			C	0.5±0.1			D	15.0±2.0			标识				
A	6.0 MAX	E	2.0±0.5																						
B	8.5 MAX																								
C	0.5±0.1																								
D	15.0±2.0																								
标识																									
绕线结构表																									
绕组	起始	结束	漆包线	圈数	绕制方式																				
N1	S	F	2UEW-0.06mm	529.5TS	圈数参考 平整密绕																				
注意事项																									
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用少字套管 4、产品底部需点胶																									
测试项目	电性范围	测试条件	测试仪器	参考值																					
电感量L	5.6mH±10%	at 25℃ 1KHz/0.25V	TH2829A	5.61																					
直流电阻DCR	39.6Ω MAX	at 25℃ 1KHz/0.25V	TH2829A	30.50																					
饱和电流Isat	L ≥ L0*90%	at 25℃ DC 40mA 1KHz/0.25V	TH2829A																						
物料	规格型号	备注	生产厂家	用量																					
磁芯	H3M DR2W4.2*6.3 2-3.2-2	镁锌材质	HUAZHONG	K																					
漆包线	2UEW(155度)		GANYUE	Kg																					
导针	0.50mm CP线		BAICHUAN	Kg																					
套管	Φ4*7.8mm UL黑色扁管		XINGQI	m																					
	Φ4.5 UL黑色扁管		XINGQI	m																					
接脚胶	FK661 黑胶 无卤		QI FU	Kg																					
无铅锡	无铅锡条		SONGBEN	Kg																					
作业流程																									
产品包装																									
包装代码																									
包装标识																									
包装物料																									
包装尺寸																									
包装说明																									
标识示意图			包装示意图																						
			<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>			制表	黄禾香	审核	饶平	确认	钟翠兰														
制表	黄禾香																								
审核	饶平																								
确认	钟翠兰																								