


客户编码		发行日期	2023-03-03																																
客户物料编码		客户规格型号	4*6-3.9UH-0.2线 长脚 黑色UL																																
样如物料编码	XR4*6-3R9M-L	样如规格型号	XR4*6-3R9M-L																																
送样数量	0PCS	送样日期	2023-03-03																																
外观尺寸 mm		<table border="1"> <tr> <td>A</td> <td>6.0 MAX</td> <td>E</td> <td colspan="2">2.0±0.5</td> </tr> <tr> <td>B</td> <td>8.5 MAX</td> <td></td> <td colspan="2"></td> </tr> <tr> <td>C</td> <td>0.5±0.1</td> <td></td> <td colspan="2"></td> </tr> <tr> <td>D</td> <td>15.0±2.0</td> <td></td> <td colspan="2"></td> </tr> <tr> <td>标识</td> <td colspan="4"></td> </tr> <tr> <td>原理图</td> <td colspan="4">  </td> </tr> </table>				A	6.0 MAX	E	2.0±0.5		B	8.5 MAX				C	0.5±0.1				D	15.0±2.0				标识					原理图				
A	6.0 MAX	E	2.0±0.5																																
B	8.5 MAX																																		
C	0.5±0.1																																		
D	15.0±2.0																																		
标识																																			
原理图																																			
 正视图 FRONT VIEW 顶视图 TOP VIEW 底视图 BOTTOM VIEW																																			
绕线结构表																																			
绕组	起始	结束	漆包线	圈数	绕制方式																														
N1	S	F	2UEW-0.20mm	13.5TS	圈数参考 平整密绕																														
注意事项																																			
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用少字套管																																			
测试项目	电性范围	测试条件		测试仪器	参考值																														
电感量L	3.9uH±20%	at 25℃ 1KHz/0.25V		TH2829A	3.99																														
直流电阻DCR	92mΩ MAX	at 25℃ 1KHz/0.25V		TH2829A	61.20																														
饱和电流Isat	L ≥ L0*90%	at 25℃ DC 1.5A 1KHz/0.25V		TH2829A																															
物料	规格型号	备注		生产厂家	用量																														
磁芯	H3M DR2W4.2*6.3 2-3.2-2	镁锌材质		HUAZHONG	K																														
漆包线	2UEW(155度)			GANYUE	Kg																														
导针	0.50mm CP线			BAICHUAN	Kg																														
套管	Φ4*7.8mm UL黑色扁管			XINGQI	m																														
	Φ4.5 UL黑色扁管			XINGQI	m																														
接脚胶	FK661 黑胶 无卤			QI FU	Kg																														
无铅锡	无铅锡条			SONGBEN	Kg																														
作业流程																																			
产品包装																																			
包装代码																																			
包装标识																																			
包装物料																																			
包装尺寸																																			
包装说明																																			
标识示意图		包装示意图																																	
		<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>				制表	黄禾香	审核	饶平	确认	钟翠兰																								
制表	黄禾香																																		
审核	饶平																																		
确认	钟翠兰																																		