









ROHS



P.C.B. LAYOUT(TOP view)

1. CURRENT RATING: 24V&5A MAX.
2. CONTACT RESISTANCE: 100 mΩ MAX.;
3. INSULATION RESISTANCE: 100MΩ MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 35N MAX.;
7. CONNECTOR UNMATING FORCES: 3N MIN.;
8. TERPROOF LEVEL: IPX7;

Model No.	DC-194-20A	DC-194-25A
PIN	φ2.0	φ2.5

④	Waterproof ring	—	1	Silica gel	White	—
③	Other Terminal	—	3	Copper alloy	Ni/Au Plating	—
②	Terminal 4#	—	1	SUS	Ni Plating	—
①	Housing	—	1	High temperature plastic	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		HRO 韩豪® ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2022.9.15		TITLE:	DC JACKS	
CHECKED				PART NO.		
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE		30~以上 10~30 5~10 ~ 5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE ±2°	DRAWING NO.	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			