



客户编码			发行日期	2023/3/31							
客户物料编码			客户规格型号	10*16-470UH-0.4线							
样如物料编码	XR10*16-471K-L		样如规格型号	XR10*16-471K-L							
送样数量	0PCS		送样日期	2023-03-23							
外观尺寸 mm	 正视图 FRONT VIEW 顶视图 TOP VIEW 底视图 BOTTOM VIEW		A	12.0 MAX	E	5.0±0.5					
			B	20.0 MAX							
			C	0.75±0.1							
			D	15.0±2.0							
			标识								
			原理图								
绕线结构表											
绕组	起始	结束	漆包线	圈数	绕制方式						
N1	S	F	2UEW-0.4mm	109.5TS	圈数参考 平整密绕						
注意事项											
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管											
测试项目	电性范围	测试条件		测试仪器	参考值						
电感量L	470uH±10%	at 25℃ 1KHz/0.25V		TH-2829A	464.00						
直流电阻DCR	0.49Ω MAX	at 25℃ 1KHz/0.25V		TH-2829A	0.38						
饱和电流Isat	L ≥ L0*90%	at 25℃ DC 1.2A 1KHz/0.25V		TH2829A							
物料	规格型号	备注		生产厂家	用量						
导针	0.75mm CP线			BAICHUAN	Kg						
磁芯	H3M DR2W10*16 5-11-5	镁锌材质		HUAZHONG	K						
漆包线	QA-1(2UEW)/155			CHANGDA	Kg						
套管	Φ10*15mm UL黑色扁管 Φ11mm UL黑色扁管			XINGQI XINGQI	m m						
接脚胶	FK661 黑胶 无卤			QI FU	Kg						
无铅锡	无铅锡条			SONGBEN	Kg						
作业流程											
产品包装											
包装代码											
包装标识											
包装物料											
包装尺寸											
包装说明											
标识示意图		包装示意图									
		<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>				制表	黄禾香	审核	饶平	确认	钟翠兰
制表	黄禾香										
审核	饶平										
确认	钟翠兰										