

客户编码				发行日期		2023-03-22																									
客户物料编码				客户规格型号		9*12-1.5UH-0.5线																									
样如物料编码		XR9*12-1R5M-L		样如规格型号		XR9*12-1R5M-L																									
送样数量		0PCS		送样日期		2023-03-22																									
外观尺寸 mm 套管 TUBE 正视图 FRONT VIEW 顶视图 TOP VIEW 底视图 BOTTOM VIEW <table><tr><td>A</td><td>10.5 MAX</td><td>E</td><td>5.0±0.5</td></tr><tr><td>B</td><td>15.0 MAX</td><td></td><td></td></tr><tr><td>C</td><td>0.65±0.1</td><td></td><td></td></tr><tr><td>D</td><td>15.0±2.0</td><td></td><td></td></tr><tr><td colspan="4">标识原理图</td></tr><tr><td colspan="4"></td></tr></table>				A	10.5 MAX	E	5.0±0.5	B	15.0 MAX			C	0.65±0.1			D	15.0±2.0			标识原理图								A	10.5 MAX	E	5.0±0.5
				A	10.5 MAX	E	5.0±0.5																								
				B	15.0 MAX																										
				C	0.65±0.1																										
				D	15.0±2.0																										
				标识原理图																											
B	15.0 MAX																														
C	0.65±0.1																														
D	15.0±2.0																														
标识原理图																															

 绕线结构表 | | | || 绕组 | | 起始 | 结束 | 漆包线 | | 圈数 | | 绕制方式 | | | |
N1		S	F	2UEW-0.50mm		5.5TS 圈数参考		平整密绕			
注意事项											
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管											
测试项目		电性范围			测试条件			测试仪器		参考值	
电感量L		1.5uH±20%			at 25℃ 1KHz/0.25V			TH2829A		1.57	
直流电阻DCR		18.8mΩ MAX			at 25℃ 1KHz/0.25V			TH2829A		14.50	
饱和电流Isat		L≥L0*90%			at 25℃ DC 5A 1KHz/0.25V			TH2829A			
物料		规格型号				备注		生产厂家		用量	
磁芯		R250 DR2W9*12 5-7.8-5				镁锌材质		LIANXING		K	
漆包线		2UEW(155度)						GANYUE		Kg	
导针		0.65mm CP线						BAICHUAN		Kg	
套管		Φ10.0mm UL黑色扁管						YIMING		m	
接脚胶		FK661 黑胶 无卤						QI FU		Kg	
无铅锡		无铅锡条						SONGBEN		Kg	
作业流程											
产品包装											
包装代码											
包装标识											
包装物料											
包装尺寸											
包装说明											
标识示意图						包装示意图					
						制表		黄禾香			
审核		饶平									
确认		钟翠兰									

文件编号: CRS-20230322-7653