



客户编码		发行日期	2023-03-23									
客户物料编码		客户规格型号	10*12-3.3UH-0.5线									
祥如物料编码	XR10*12-3R3M-L	祥如规格型号	XR10*12-3R3M-L									
送样数量	0PCS	送样日期	2023-03-23									
外观尺寸 mm 		A	12.0 MAX	E	5.0±0.5							
		B	15.5 MAX									
		C	0.75±0.1									
		D	15.0±2.0									
		标识										
		原理图										
绕线结构表												
绕组	起始	结束	漆包线	圈数	绕制方式							
N1	S	F	2UEW-0.5mm	7.5TS	圈数参考	平整密绕						
注意事项 1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管												
测试项目	电性范围		测试条件		测试仪器	参考值						
电感量L	3.3uH±20%		at 25℃ 1KHz/0.25V		TH-2829A	2.97						
直流电阻DCR	23mΩ MAX		at 25℃ 1KHz/0.25V		TH-2829A	17.60						
饱和电流Isat	L ≥ L0*90%		at 25℃ DC 4A 1KHz/0.25V		TH2829A							
物料	规格型号		备注		生产厂家	用量						
导针	0.75mm CP线				BAICHUAN	Kg						
磁芯	H3M DR2W10*12 5-7.2-5		镁锌材质		HUAZHONG	K						
漆包线	QA-1(2UEW)/155				CHANGDA	Kg						
套管	Φ10*15mm UL黑色扁管				XINGQI	m						
	Φ11mm UL黑色扁管				XINGQI	m						
接脚胶	FK661 黑胶 无卤				QI FU	Kg						
无铅锡	无铅锡条				SONGBEN	Kg						
作业流程												
产品包装												
包装代码												
包装标识												
包装物料												
包装尺寸												
包装说明												
标识示意图			包装示意图									
			<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>				制表	黄禾香	审核	饶平	确认	钟翠兰
制表	黄禾香											
审核	饶平											
确认	钟翠兰											