



电气特性:Electrical:

- 1.额定电流 : Current Rating
1.5A/contact terminal
- 2.额定电压 : Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
30 milliohms MAX
- 4.耐电压:Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 5.绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力 : Connector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:0.7kgf(MIN)
- 2.端子保持力 : Terminal Retention
1.2kgf(MIN)
- 3.寿命: 1500次

原材料:Material:

- 1.塑胶:Housing: LCP NC
 - 2.端子:Contact:Copper Alloy C2680
 - 3.外壳:Shell:C2680
- 电镀:Finish:

- 1 端子Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
- 2 外壳Shell: Nickel 50u" Min plating over all.

产品图

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

公差一览表	
TOLERANCE UNLESS OTHERWISE	公差一览表
X	±0.25
.X	±0.20
.XX	±0.15
.XXX	±0.10

单位	MM	制图	L-S-S	产品料号
UNITS	MM	DRAWING	L-S-S	904-132A2031S10100
比例	1:1	审核	CHKD	产品名称
SCALE	1:1	核准	APPD	角法
日期	2015/10/20			版本
DATE	2015/10/20			VER

深圳市精拓金电子有限公司