




MAPX	MODIFICATION	DATE
------	--------------	------



P C B

- 电气特性:Electrical:
1. 额定电流: Current Rating
1.5A/contact terminal
 2. 额定电压: Voltage Rating
30V DC
 3. 接触阻抗: Contact Resistance
30 milliohms MAX
 4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN
- 物理性能: Mechanical:
1. 插拔力: Connector Mate and Umate Force
Mate force: 3.57kgf (MAX)
Umate force: 1.02kgf (MIN)
 2. 端子保持力: Terminal Retention
1.2kgf (MIN)
 3. 寿命: 1500次
- 原材料: Material:
1. 塑胶: Housing: PA9T 绿
 2. 端子: Contact: Copper Alloy C2680
 3. 外壳: Shell: SPCC
- 电镀: Finish:
1. 端子 Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
 2. 外壳 Shell: Nickel 50u" Min plating over all.

产品图

深圳市精拓金电子有限公司

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

公差一览表		单位		制图		制图料号	
TOLERANCE	UNITLESS	OTHERWISE	UNITS	DRAWING	DESIGNER	PRODUCT PART NO.	916-361A3094Y40200
X	±0.30	X	MM	审核	林属升	产品名称	
X	±0.25	X	比例	制图	郭志富	PRODUCT NO.	
.XX	±0.15	.XX	1:1	核准	黄国荣	角法	
.XXX	±0.10	.XXX	日期	APRD	2019.11.23	版本	A0
	±0.5		DATES			VER	

