



目 录 MAPX	设 变 内 容 MODIFICATION	日 期 DATE



电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectric Withstanding Voitage:
500 V AC AT Sea Level
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:




1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
2. 端子保持力: Terminal Retenion
1.2kgf (MIN)
3. 寿命: 1500 次

原材料:Material:

1. 塑胶:Housing:LCP BK
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC

电镀:Finish:

1. 端子Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.



产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司							
Pin NUMBER	SIGNAL NAME	公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	林属升	产品料号 PRODUCT PART NO.	910-151A2026S10200
1	VBUS	X.	±0.25	X'	±5°	比例 SCALE	审核 CHKD	产品名称 PRODUCT NO.	AF10.0C 款前两脚有边铁壳 LCP 黑胶 6.2SMT 无耳朵
2	D-	.X	±0.20	.X'	±2°				
3	D+	.XX	±0.15	.XX'	±1°	日期 DATE	核准 APPD	角法 VIEW	版本 VER
4	GND	.XXX	±0.10	.XXX'	±0.5°				
						2015/10/20	黄国荣		A0