



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥


- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	8
2	黑色	7
3	黄色	6
4	白色	5
5	绿色	4
6	蓝色	3
7	紫色	2
8	灰色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X9821HM-08A-N0HF	2PCS		
2	X9821TF-PSN	16PCS		
3	UL1571/28AWG. 红. 黑. 黄. 白. 绿. 蓝. 紫. 灰色	各1PCS	100MM	
总量				

⑥ 正反接 (Positive and negative) Z (反接)/F (正接)								DSND		SCALE: N/A	DRAWING NO.				
					ANGLAR			±5°	DWN		VIEW: 	X9821TF-PSN-A28RBYWGLPE-L100-X9821TF-F			
Δx					L≤ 4			±0.2	CHKD		UNIT: mm/in	PART NO.:			
Δx					4<L≤ 16			±0.3	APPD		SIZE: A4	DWG NO.:			
Δx					16<L≤ 63			±0.4							
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L> 63	±0.5	XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
REVISIONS							UNSPECIFIED TOLERANCES							1/1	A0
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn															