



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	7
2	黑色	6
3	黄色	5
4	白色	4
5	绿色	3
6	蓝色	2
7	紫色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X9821HM-07A-N0HF	2PCS		
2	X9821TF-PSN	14PCS		
3	UL1571/28AWG. 红. 黑. 黄. 白. 绿. 蓝. 紫色	各1PCS	300MM	
总量				

⑥ 正反接 (Positive and negative) Z (反接) / F (正接)						DSND		SCALE: N/A		DRAWING NO.		
						DWN		VIEW: 		X9821TF-PSN-A28RBYWGLP-L300-X9821TF-F		
Δx						CHKD		UNIT: mm/in		PART NO.:		
Δx						APPD		SIZE: A4		DWG NO.:		
Δx												
MARK		DESCRIPTION		DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			
REVISIONS										WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn											1/1	A0
						ANGLAR		±5°				
						L≤ 4		±0.2				
						4<L≤ 16		±0.3				
						16<L≤ 63		±0.4				
						L> 63		±0.5				