



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
③ 线规线色 (Wire gauge line color) A: (AWG32-AWG28)
Circuit: R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
④ 线长 (Line length) L:(可定制长度)
⑤ 系列 (Series No)
⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	9
2	黑色	8
3	黄色	7
4	白色	6
5	绿色	5
6	蓝色	4
7	紫色	3
8	灰色	2
9	棕色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X9821HM-09A-N0HF	2PCS		
2	X9821TF-PSN	18PCS		
3	UL1571/28AWG. 红. 黑. 黄. 白. 绿. 蓝. 紫. 灰. 棕色	各1PCS	100MM	
总量				

⑥ 正反接 (Positive and negative) Z(反接)/F (正接)								DSND		SCALE: N/A	DRAWING NO.				
											X9821TF-PSN-A28RBYWGLPEN-L100-X9821TF-F				
								DWN		VIEW: 	PART NO.:				
Δx								CHKD		UNIT: mm/in					
Δx								APPD		SIZE: A4	DWG NO.:				
Δx															
MARK		DESCRIPTION			DATE	REVISED	APPROVED	L > 63		±0.5					
REVISIONS								UNSPECIFIED TOLERANCES							
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn								XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
														1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-dg.cn						