



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X  
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)  
Circuit:R(red)/B (black) /Y (yellow) /G (green) /  
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

| A | 颜色 | B |
|---|----|---|
| 1 | 红色 | 7 |
| 2 | 黑色 | 6 |
| 3 | 黄色 | 5 |
| 4 | 白色 | 4 |
| 5 | 绿色 | 3 |
| 6 | 蓝色 | 2 |
| 7 | 紫色 | 1 |

3. MATERIAL(材料)

| 标志 | 料号                                       | 单用量   | 备注    | 总用量 |
|----|------------------------------------------|-------|-------|-----|
| 1  | X9821HM-07A-N0HF                         | 2PCS  |       |     |
| 2  | X9821TF-PSN                              | 14PCS |       |     |
| 3  | UL1571/28AWG.<br>红. 黑. 黄. 白.<br>绿. 蓝. 紫色 | 各1PCS | 100MM |     |
| 总量 |                                          |       |       |     |

|                                                   |  |             |  |      |         |          |                        |                                                                                             |                                      |                                       |       |          |
|---------------------------------------------------|--|-------------|--|------|---------|----------|------------------------|---------------------------------------------------------------------------------------------|--------------------------------------|---------------------------------------|-------|----------|
| ⑥ 正反接 (Positive and negative) Z (反接) / F (正接)     |  |             |  |      |         | DSND     |                        | SCALE: N/A                                                                                  |                                      | DRAWING NO.                           |       |          |
|                                                   |  |             |  |      |         | DWN      |                        | VIEW:  |                                      | X9821TF-PSN-A28RBYWGLP-L100-X9821TF-F |       |          |
| <div>Δx</div>                                     |  |             |  |      |         | CHKD     |                        | UNIT: mm/in                                                                                 |                                      | PART NO.:                             |       |          |
| <div>Δx</div>                                     |  |             |  |      |         | APPD     |                        | SIZE: A4                                                                                    |                                      | DWG NO.:                              |       |          |
| <div>Δx</div>                                     |  |             |  |      |         |          |                        |                                                                                             |                                      |                                       |       |          |
| MARK                                              |  | DESCRIPTION |  | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |                                                                                             | XKB INDUSTRIAL PRECISION CO.,LIMITED |                                       |       |          |
| REVISIONS                                         |  |             |  |      |         |          |                        |                                                                                             |                                      | WEIGHT                                | SHEET | REVISION |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |  |             |  |      |         |          |                        |                                                                                             |                                      |                                       | 1/1   | A0       |