




NOTES 注释:

1. MATERIAL 材料:

1.1 INSULATION 绝缘材料: PA9T (KUARARY GN2330)
WITH 30% GF, UL94V-0,

COLOR 颜色: SEE PART No..

TINE PLATE 齿板: LCP (ZENITE 5145L OR E471i)
WITH 30% GF, UL94V-0

COLOR 颜色: SEE PART No..

1.2 CONTACTS 触点: PHOSPHOR BRONZE,
C5191R-H, T=0.25mm

2. FINISH 饰面:

2.1 CONTACT 触点:

SELECTEIVE GOLD PLATING ON CONTACT AREA.
100μ" MIN. MATTE TIN PLATING ON SOLDER TAILS
50μ" MIN. NICKEL UNDERPLATING OVERALL.

X3091 W R - XX X - 9T V01

① ② ③ ④ ⑤ ⑥ ⑦

① Series Nunber

② Terminal form: WAFER

③ Welding Board Angle : R-90°

④ No. of Pins: XX-36~164 Pin

⑤ Tail Length (DIM "E") :A :2.30mm
B:3.1mm

⑥ Plastic material: PA9T/PA46 UL94V-0

⑦ Contact Plating: V01-Gold Flash
V15-Gold 15"u"
V30-Gold 30"u"


DIMENSIONS				
POSITION	N	B±0.15	C±0.15	D±0.23
36	6	7.65	9.15	25.00
64	20	21.65	23.15	39.00
98	37	38.65	40.15	56.00
164	70	71.65	73.15	89.00

XKLB



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X3091WR-XXX-9TV01
CHKD	UNIT: mm/in	DWG NO.: X-X3091WR-XXX-9TV01
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L≤ 4 ±0.2
ΔX					4<L≤ 16 ±0.3
ΔX					16<L≤ 63 ±0.4
ΔX					L> 63 ±0.5
MARK	REVISIONS				
	www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				



DIMENSIONS				
POSITION	N	C	F±0.20	G
36	6	9.15	8.15	B PIN#17
64	20	23.15	22.15	B PIN#31
98	37	40.15	39.15	B PIN#48
164	70	73.15	72.15	B PIN#81



							DSND		SCALE: N/A	MODEL TYPE:		
ΔX					ANGLAR	±5°		DWN		VIEW: 	PART NO.:	
ΔX					L ≤ 4	±0.2		CHKD		UNIT: mm/in	X3091WR-XXX-9TV01	
ΔX					4<L ≤ 16	±0.3					DWG NO.:	
					16<L ≤ 63	±0.4					X-X3091WR-XXX-9TV01	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5		APPD		SIZE: A4		
REVISIONS							UNSPECIFIED TOLERANCES			WEIGHT		
www.helloxkb.com www.helloxkb.cn www.xk-da.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED			SHEET		
										1/1		
										A0		