



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1502H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X

① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
④ 线长 (Line length) L:(可定制长度)
⑤ 系列 (Series No)
⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	2
2	黑色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1502H-02A-N 0	2PCS		
2	X1502T-PSN	4PCS		
3	UL1007/28AWG. 红. 黑色	各1PCS	200MM	
总量				

⑥ 正反接 (Positive and negative) Z(反接)/F (正接)								DSND		SCALE: N/A	DRAWING NO. X1502T-PSN-A28RB-L200-X1502T-F				
Δx					ANGLAR			±5°	DWN		VIEW: 	PART NO.:			
Δx					L≤ 4			±0.2	CHKD		UNIT: mm/in	DWG NO.:			
Δx					4<L≤ 16			±0.3							
Δx					16<L≤ 63			±0.4							
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L> 63	±0.5	APPD		SIZE: A4				
REVISIONS						UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														1/1	A0