



1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1502H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X

① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	8
2	黑色	7
3	黄色	6
4	白色	5
5	绿色	4
6	蓝色	3
7	紫色	2
8	灰色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1502H-08A-N0	2PCS		
2	X1502T-PSN	16PCS		
3	UL1007/28AWG. 红, 黑, 黄, 白, 绿, 蓝, 紫, 灰色	各1PCS	200MM	
总量				

⑥ 正反接 (Positive and negative) Z(反接)/F (正接)							DSND		SCALE: N/A	DRAWING NO.		
					ANGLAR	±5°				X1502T-PSN-A28RBYWGLPE-L200-X1502T-F		
Δx					L≤ 4	±0.2		DWN		VIEW: 	PART NO.:	
Δx					4<L≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.:	
Δx					16<L≤ 63	±0.4		APPD		SIZE: A4		
MARK	DESCRIPTION			DATE	REVISED	APPROVED		L> 63	±0.5			
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn										WEIGHT	SHEET	REVISION
											1/1	A0