





使用温度范围 (Ambient temperature Range):-25°~+85°		孔位	A	B		
适用线规 (Applicable Wires):AWG 28#~20#		2	0	5.4		
适用基板厚度 Applicable PCboard thickness):1.7mm		4	4.2	9.6		
额定电压 (Voltage rating):300V AC,DC		6	8.4	13.8		
额定电流 (Current rating):4A		8	12.6	18.0		
接触电阻 Contact Resistance):<0.015Ω		10	16.8	22.2		
绝缘电阻 (Insulation Resistance):>1000MΩ		12	21.0	26.4		
耐压 (Withstand Voltange):1000V/min		14	25.2	30.6		
材料 (Material) 1.基座: PA66 FV2 2.插针: 黄铜		16	29.4	34.8		
		18	33.6	39.0		
		20	37.8	43.2		
		22	42.0	47.4		
		24	46.2	51.6		

9357WR-2XXP	PA66	9357H	9357T
PART NO	Material	Suitable Housing	Suitable Terminal

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	9357WR-2XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	H-9357WR-2XXP			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	