

5

4

3

2






1

D


C

B


A



Cable diameters




Cable diameters



Scale: 2:1

Maximum cable outer diameter without grommet: 11,5 mm

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, top entry hood with knurled screws, 9 poles, thermoplastic metallized	Maßstab/ Scale 1:1 2:1
			Detail.	28/03/02	CV			
			Insp.					
			Stand.					
34784	12/02/08	PK	HARTING EURL F-95972 Paris				TB 09 67 009 0425	Blatt/ Page 1 / 1
32346	24/10/04	TR						
29760	28/03/02	CV						
Mod.	Dat.	Name					Sub.	