




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
05	△△	新增CAP配方	27.5.2008	許承佑
06	△△	變更新料號	2009.03.12	王群祥
07	△△	變更圖號與注解	2011.07.19	黃明霞
08	△△	為防止方形膠紙鬆脫,變更為圓形膠紙	2012.08.29	黃小燕
09	△△	依業務要求增加接觸點的尺寸標註位置	2019.10.22	何東華




Specifications
Current Rating:1Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:300VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
△△ Contact Material:Phosphor Bronze
Insulator Material:High Temperature Thermoplastic, UL 94V−0 LCP or the equivalent material △△
All materials must meet Greenconn requirement for environment protection.

Ordering Information

C SEA202 − XX XX A 001 C 1 A X
No. of Pins per Row
02~50
Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin
Color
1=Black
Standard Packing
C=Tube
Selective Packing
A=box
E=Cap+Tube
F=Cap+Tape&Reel
G=Acetate Tape+Tube
H=Acetate Tape+Tape&Reel

Recommended P.C.Board Layout
(Tolerance:±0.05)



格 菱 股 份 有 限 公 司 Greenconn Corporation			GENERAL TOLERANCE		DESIGNED: 何東華	DWG. NO.	△△ △△ CSEA202−CA1CA	TITLE.
REV.	UNIT.	SCALE.	PAGE.		CHECKED:	DATE:		1.27 FEMALE HEADER
09	mm	3:1	1/1		CO SIGNED: 廖世龍	DATE: 2019.10.22	PART NO.	DUAL ROWS DIP TYPE
					APPROVED:	DATE:	CSEA202−XXXX A001C1AX	CONNECTOR