

## Han A Hood Top Entry 2 Pegs M20



Image is for illustration purposes only. Please refer to product description.

### Identification

|                          |                |
|--------------------------|----------------|
| Category                 | Hoods/Housings |
| Series of hoods/housings | Han A®         |
| Type of hood/housing     | Hood           |

### Version

|                      |   |
|----------------------|---|
| Size                 | 3 A   |
| Version              | Top entry   |
| Cable entry          | 1x M20  |
| Locking type         | Single locking lever                                |
| Field of application | Standard Hoods/housings for industrial applications |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                    |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E     | 12   |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast        |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |
| RoHS                    | compliant            |
| ELV status              | compliant            |

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| China RoHS                           | e              |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Not contained  |
| California Proposition 65 substances | Yes            |
| California Proposition 65 substances | Nickel<br>Lead |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
| CE        | Yes    |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 10                                       |
| Net weight                     | 20 g                                     |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |