






ZX-SIM-482.5J



Reference PCB layout  
Unit: mm tolerance: ±0.05



◎ SPECIFICATION:

- 壽命:10000Cycles Min.
- Contact Force:0.2~1.0N. (卡片厚度0.76mm)
- 接觸阻抗:50mΩ, typical,100mΩ Max.
- 絕緣阻抗:Min 1000MΩ/500V DC.
- open/lock force: 1.5~3.5N(IR前)
- 平貼:IR前後CP8 0.10mm Max;塑膠0.20mm Max.
- ◎為重點檢驗尺寸.

Table A

料號	燐鑫	ICA-521-110201-541
	漢門	ICA-521-110211-541M
材質	塑膠	LCP E130i BK HF
	端子	C5210R-H T=0.20mm HF
端子電鍍	整體打鍍底50u"Min,接觸區刷金3u"Min, 焊接區浸鍍純霧錫100u"Min.	

兆星精密电子(深圳)有限公司

物料編號 PART NO.		ZX-SIM-482.5J		材質 MATERIAL	See Table A	機種型號 MODEL NO.	
核准 APPROVED	Lin R	230521	圖名 TITLE	翻蓋式 MiniSIM卡卡座全塑			
審核 CHECKED	Lin L	230521	圖號 DRAWING NO.	ZX-SIM-482.5J			
設計 DESIGNED	Lin L	230521	圖紙 SIZE	A4	比例 SCALE	1/1	SHEET 1 OF 1
符號 SYM.	日期 DATE	內 容 DESCRIPTION OF REVISIONS		繪圖 DRAWN	核准 APPROVED	第三角 3RD. ANGLE'S	
		LENGTH	ANGULAR		單位 UNIT	mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED		0.00	±0.08	0.00°	±1'		
		0.0	±0.10	0.0°	±2'		
		0.0	±0.15	0°	±3'		
		0.	±0.20				