



NOTE:
 1. Material & Finish See Table;
 2. Circuit Diagram For Switch



3. Characteristic:
 3-1.Current Rating :1A max.
 3-2.Contact Resistance:50mOhms max
 3-3.Insulation Resistance:1000M0hmsΩ min./500VDC
 3-4.Dielectric Withstanding Voltage:500VAC/1minute
 3-5.Mating Force: 8N Max, Withdrawal Force: 1N Min.;
 3-6.Durability: 3000 Cycles
 3-7.Operating Temperature:-25°C to+85°C
 4. Critical Dimensions Marked ▼ " Should Check By QC.
 5. Please Contact PROMAX Sales Representative to Verify Product Details.



6	Shell	Stainless Steel	Nickel Under Plated Overall.
5	Lever	Stainless Steel	/
4	Cam	Stainless Steel	/
3	Housing	Thermoplastics	Black,UL94V-0
2	Detect	Copper Alloy	Gold Flash on Solder Tails ; Gold Flash on Contact Area;
1	Terminal	Copper Alloy	Nickel Under Plated Overall.
Item	Part Name	Material	Description

兆星精密电子 (深圳) 有限公司

E TITLE: 卡托式 MicroSIM卡 卡座

PART NO. ZX-MSIM-281.55J

PRODUCT SPEC. MICRO SIM CARD

FILE NAME.

SCALE 1:1 UNIT:mm A4 SHEET:1 of 1

NEW RELEASE		GENERAL TOLERANCE UNLESS OTHERWISE NOTED		DESIGN CHECK		APPRO.	
工程变更通知单号 ECN(DCN) NO.	版次 REV	日期 DATE	说明 DESCRIPTION	改变 CHANGE	承认 APPRO.	设计 DESIGN	校阅 CHECK