





PIN No.	PIN NAME
C8	RESERVED
C7	I/O
C6	VPP
C5	GND
C4	RESERVED
C3	CLK
C2	RST
C1	VCC



NOTES:

- ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING: 0.5 Amp. MAX.
 - VOLTAGE: 100V DC. MAX.
 - LDV LEVEL CONTACT RESISTANCE: 100 mOhms MAX. INITIALLY.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN. FOR 1 MINUTE.
 - INSULATION RESISTANCE: (INITIAL) 1000Mhms MIN. (FINAL) 100Mhms MIN. BY APPLYING 500V DC ON MATED AND UNMATED CONNECTORS THROUGH MIL-STD-202, METHOD 302.
- MECHANICAL CHARACTERISTICS:
 - DURABILITY: 5000 CYCLES.
 - OPERATING TEMP. RANGE: -25°C TO 85°C. [INCLUDING TERMINAL TEMP. RISE]
 - STORAGE TEMP.: -40°C TO 85°C.
- DIMENSIONS MARKED ∇ ARE MAJOR CHECKED DIMENSIONS.
- HARMFUL MATERIAL CONTROL PLEASE FOLLOW DDC. NO. 'EPI12'.

兆星精密电子(深圳)有限公司

PRODUCT SPEC. MICRO SIM CARD

TITLE: 自弹式 MicroSIM卡 卡座 6P

PART NO. ZX-MSIM-481.35J-Z6

FILE NAME:

SCALE 1:1 UNIT:mm A4 SHEET: 1 of 1

General	Angle	设计
X±0.50	X°±2°	DESIGN
.X±0.30	.X°±1°	校阅
.XX±0.20	.XX°±0.5°	CHECK
		承认
		APPRO.

工程变更通知单号 ECN(DCN) NO.	版次 REV	日期 DATE	说明 DESCRIPTION	改变 CHANGE	承认 APPRO.

GENERAL TOLERANCE UNLESS OTHERWISE NOTED