


NOTES:

- 1.MATERIAL:
 - 1.1 Housing: High Temperature Thermoplastic UL94V-0,Color:Black
 - 1.2 Terminal:Copper Alloy
 - 1.3 Stator:Copper Alloy
 - 1.4 Shell:Stainless Steel.
- 2.SPECIALITY:
 - 2.1 Rated Current:1.0A
 - 2.2 Rated Voltage:30V
 - 2.3 Contact Resistance:50mΩ Max
 - 2.4 Insulation Resistance:100MΩ Min 100V DC
 - 2.5 Dielectric Withstanding Voltage:100V AC
 - 2.6 Solder Ability:245±5°C;5±0.5s
 - 2.7 Durability:5000 cycles
 - 2.8 Operating Condition:Temperature:-30°C~+80°C; Humidity:80%RH Max



RECOMMENDED PCB LAYOUT DIMENSIONS:±0.05

兆星精密电子 (深圳) 有限公司

					零件名称 TITLE	X ± 0.50 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.08	X' ± 2 X.X' ± 1 X.XX' ± 0.5	第三角投影法 THIRD ANGLE REFLECTION METHOD	图次 REV
					零件料号 PART NO.	一般公差 GENERAL TOLERANCE		比例: 比例: SCALE: SCALE:	图次 SHEET
B	修改字体位置	Lin R	23/05/21		PART-NO. ZX-TF-281.6J	出图日期 PLOT DATE	核准 APPROVED BY	审核 CHECKED BY	设计 DESIGNER BY
A	新发行				图号 DRWG-NO.	23/05/21 MM-DD	核准: Lin R	审核: Lin R	设计: Lin R
图次 REV	变更单号 ECN NO	变更描述 DESCRIPTION	确认 APPROVA BY	日期 REV					图次 SHEET