










1. PACKAGING: REEL
2. SUITABLE FOR PIN CONTACT: SEE DRAWING 2349180

2-2349177-2	C	4.0~6.0mm ²	2	SPRING	Cu-ALLOY	Ag	21.5	4.5	5.83	5.33	2.9
			1	BODY	Cu-ALLOY	Ag					
2-2349177-1	C	2.5mm ²	2	SPRING	Cu-ALLOY	Ag	21	4	5.02	4.63	2.3
			1	BODY	Cu-ALLOY	Ag					
1-2349177-2	C	4.0~6.0mm ²	2	SPRING	Cu-ALLOY	Ag	21.5	4.5	5.83	5.33	2.9
			1	BODY	Cu-ALLOY	SnAg					
1-2349177-1	C	2.5mm ²	2	SPRING	Cu-ALLOY	Ag	21	4	5.02	4.63	2.3
			1	BODY	Cu-ALLOY	SnAg					
PART NO.	REVISION	WIRE RANGE	ITEM	DESCRIPTION	MATERIAL	FINISH	DIM. A	DIM. B	DIM. C	DIM. D	DIM. E

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J.YIN 30AUG2021	TE Connectivity NAME DIA. 4MM SOCKET CONTACT						
DIMENSIONS: mm				CHK W.ZHANG 30AUG2021							
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3				APVD I.YIN 30AUG2021							
DIMENSIONS: mm				PRODUCT SPEC							
MATERIAL SEE TABLE				108-32306	SIZE CAGE CODE DRAWING NO						RESTRICTED TO
SEE TABLE				APPLICATION SPEC	A 00779 C=2349177						-
SEE TABLE				116-160038	CUSTOMER DRAWING						SCALE 10:1 SHEET 1 OF 1 REV C
SEE TABLE				WEIGHT -							