




Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE ±0.05)




SPECIFICATIONS

Rated Current: 1.0AMP
Contact Resistance: 20mΩ Max
Withstand Voltage: 500V AC/DC
Insulation Resistance: 1000MΩ Min
Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
Contact Plating: Au Over Ni
Insulator Material: Polyester (UL94V-0)
Standard: PA6T
Max. Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Ordering Information



| | | | | | | | | | | | |
|-----------|------------------------|-------------------|-------------------|-------|-------------------|--|---|--|--------------------|--------------|-----|
| | | | GENERAL TOLERANCE | | 制 图 DRAWING | | 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD | | | | |
| | | | DIM | TOL | 审 核 CHECK | | 产品名称 TITLE | | 1.27双排 排母 贴片 | 版本 REV. | A |
| | | | X. X | ±0.30 | 批 准 APPROVAL | | 产品料号 PART NO. | | PM127-2-N-S-4.3-XX | 单 位 UNITS | mm |
| | | | X. XX | ±0.20 | 比 例 SCALE | | 材 料 MATERIAL | | | 页 次 SHEET | 1/1 |
| | | | X. XXX | ±0.10 | 投 影 Projection | | | | | | |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | Angle ±3.0° | | | | | | | | |