



Materials
 Pin: Brass,machined,(H59-3)
 Plating:Gold plated: 1.25u”m/50u”nickel,full gold
 Insulator body(black): PPS(UL94V-0)

Electrical
 Current rating: 3 Amps/contact max.
 Contact resistance:20mΩ
 Insulation resistance:1000MΩ
 Operating voltage:60 AC/DC

Mechanical
 Operating temperature :Gold plated:-55C to +105C
 (Continuous) -67”H to +105”H
 Tin plated:-40°C to +105°C
 Soldering temperature:260°C,10s max

Ordering Information

PZ 254 - * - N - Z - ** - C

No.of Rows 1=Single Row 2=Dual Row	No.of Pins 2-40Pin	Type Z-直排 N-排针 W-弯脚 R-弯脚	Contact Plating G0:Gold Flash G1:1u” Gold G2:3u” Gold G3:5u” Gold G4:10u” Gold G5:15u” Gold G6:30u” Gold S0:Gold Flash/Tin S1:Tin	Round Pin (圆针)
--	-----------------------	--------------------------------------	--	-------------------

			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	2.54 双排 直排针 塑高3.0 (上针0.6 下针0.5)	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	PZ254-2-N-Z-XX-C	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1