






REV	MARK	修改摘要	签名	日期
AO		NEW DWG		2016-03-12



**SPECIFICATIONS**

- OPERATING CURRENT: 0.5A MAX.
- OPERATION TEMPERATURE: -25°C TO +85°C
- DIELECTRIC WITHSTANDING VOLTAGE:  
500Volts AC BETWEEN ADIACENT TERMINAL(UNMATE)  
300Volts AC BETWEEN ADIACENT TERMINAL(MATE)
- INSULATION RESISTANCE:  
100Mohm MIN.(UNMATED);10Mohm MIN.(MATED)
- HDMI SPECIFICATION COMPLIANCE
- 盐雾测试: 国际标准要求, 温度35°C, 浓度5%的盐水, 24H, 用清水洗净后观测, 产品无氧化、无锈蚀
- 寿命测试: ≥10000次



ROHS COMPLIANCE

ITEM	NAME	Q'TY	NOTES
4	DUST COVER	1	THERMOPLASTIC UL94V-0
3	CONTACTS	19	COPPER ALLOY, GOLD PLATED OVER NICKEL ON CONTACT AREA AND 100u" MIN. TIN PLATED OVER NICKEL ON SOLDER TAILS
2	HOUSING	1	THERMOPLASTIC UL94V-0
1	SHELL	1	SPCC,NICKEL PLATED

**深圳市华德共创科技有限公司**  
Shenzhen Huade co-create Technology Co.,LTD  
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: HDMI 立式母座13高 铁壳镀 产品名称: 镍黑胶	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDMI-GD-118PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001