



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25°C-+85°C

温度范围: -25°C-+85°C

Insulation resistance:≤10mΩ min

绝缘电阻: ≤10mΩ min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2510 W R -XX A -N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:R- 90°

4..Row No-Pin No:XX-02P~20P

5.TYPE:B

6.Material:N0-PA99 94V-0

7.Plating Category:SN-Bright Tin Plating

poles	Dimensions/mm	
	A	B
02	2.54	5.08
03	5.08	7.62
04	7.62	10.16
05	10.16	12.70
06	12.70	15.24
07	15.24	17.78
08	17.78	20.32
09	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48
13	30.48	33.02
14	33.02	35.56
15	35.56	38.10

X2510WR-XXA-N0SN	N0-Nylon66	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKI Terminal

DSND	SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connect
DWN	VIEW:	PART NO.: X2510WR-XXA-N0SN
CHKD	UNIT: mm/in	DWG NO.: X2510WR-XXA-N0SN
APPD	SIZE: A4	

XKIB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISI
	1/1	A0

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	UNSPECIFIED TOLERANCES
ANGLAR ±5°	
L ≤ 4 ±0.2	
4 < L ≤ 16 ±0.3	
16 < L ≤ 63 ±0.4	
L > 63 ±0.5	
DATE	REVISED
DATE	APPROVED
DATE	APPROVED

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn