


P.C.B LAYOUT

Specifications:

规格:  
**Current rating:**5A AC/DC  
 额定电流: 5A AC/DC  
**Voltage rating:**250V AC  
 额定电压: 250V AC  
**Withstanding voltage:**500V AC/MIN  
 耐受电压: ≥500V AC/分钟  
**Temperature range:**-55°C~+105°C  
 温度范围: -55°C~+105°C  
**Insulation resistance:**1000MΩMIN  
 绝缘电阻: ≥1000MΩ  
**Contact resistance:**30mΩMAN  
 接触电阻: ≤30mΩ  
**Material And FINISHED:**  
 材料和成本:  
**INSULATOR:**PBT UL 94V-0  
 绝缘体: PBT UL 94V-0  
**SHELL:** SPCC-SD Plated Ni / Au / Sn  
 外壳: 铁合金 镀镍/金/锡  
**CONTACT MATERIAL:**COPPER ALLOY  
 触点材料: 铜合金

X03 XX F C X X X  
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No. Pin No: XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ C: Car-pin
- ⑤ Planting Category:1:1U' ;2:2U' ;3:3U' ;4:5U' ;5:15U' 6:30U' ;7:AuSn
- ⑥ B:Black W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2



NO.OF CONTACT	A±0.25	B±0.13	C±0.38	D
09	16.33	24.99	30.81	11.08
15	24.66	33.32	39.14	19.39
25	38.38	47.04	53.04	33.24
37	54.84	63.50	69.32	49.86

广东星坤科技股份有限公司  
 生效 MARK 日期  
 文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

UNSPECIFIED TOLERANCES

DSND	SCALE: N/A	MODEL TYPE: D-USB
DWN	VIEW:	PART NO.: X03XXFCXXX
CHKD	UNIT: mm/in	DWG NO.: X-X03XXFCXXX
APPD	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED		1/1 A0