



REV	ECR#	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A0	~	NEW DESIGN			
A1	~	ADD NEW SPECIFICATIONS			
A3		ADD COLOR OF HOUSING			



NOTES :

- 1.0. RATING :
- 1.1. VOITAGE :60 VAC (R.M.S.)
 - 1.2. NOMINAL CHARACTERISTIC IMPEDANCE: 50 Ohm
 - 1.3. APPLICABLE FREQUENCY: DC ~ 6GHz
 - 1.4. VSWR: 1.3 MAX. (DC~3GHz), 1.5 MAX. (3~6GHz)
 - 1.5. TEMPERATURE : -40°C TO +85°C
 - 1.6. APPLIED TO IR SOLDERING PROCESS
- 2.0. MATERIAL SEE BILL OF MATERIAL :
- 2.1.HOUSING: THERMOPLASTIC,UL94V-0,
 - 2.2.CENTER CONTACT : COPPER ALLOY.
 - 2.3.SHELL CONTACT: COPPER ALLOY.

RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.05)

 CENTER CONTACT
 GROUND CONTACT

PRODUCT SPEC:
PACKAGE SPEC:

CONTROL POINT FAI : to CRITICAL (Cpk & Cp) : EX) = Places MAJOR (QC CHECKED) : ▼ = Places TOOL DESIGN DIMENSION : [T DIM] = Places EVALUATE REPORTES NUMBER NUMBER	TOLERANCES UNLESS OTHERWISE SPECIFIED GENERAL X ±0.30 XX ±0.25 XXX ±0.15 ±0.05 ANGLES X ±3.0° XX ±2.0° XXX ±1.0°	DRAWING DATE	 兆星精密电子(深圳)有限公司 TITLE IPEX 内针 一代板端 IPEX1座子 SERIES ZX-RF-1-Z21.25X DRAWING NO
	SCALE 1:1	DESIGN DATE	
	SHEET 1/1	CHECK DATE	
	UNIT mm	APPROVED DATE	
		3D FILE	SIZE A3 REV A3