




A	B	C	D	E	F
				NEW DWG	2016-03-12
修订 REV A0	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE	




SECTION A-A





SPECIFICATION:


1. RATING: DC 20V 7A
2. CONTACT RESISTANCE: 30mΩ MAX.
3. INSULATION RESISTANCE: 100 MΩ MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 3N~30N
6. EXTRACTION FORCE: 3N~30N
7. DURABILITY: 5,000 CYCLES



RECOMMENDED PCB LAYOUT (t=1.00)
TOP VIEW TOLERANCE: ±0.05



SCHEMATIC	
○ 1# (+)	C CENTER PIN BRASS GOLD FLASH" / Ni 40u"
○ 2#/3#/4#/5# (-)	B SHELL COPPER ALLOY Ni 40u"
△	A HOUSING HIGH TEMP.THERMOPLASTIC BLACK
NO.	DESCRIPTION MATERIAL REMARKS QTY

MATING PLUG
DP400170-0038-6H

深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES-		TITLE: DC Power Jack 4017 大电流8A, 卧式, 产品名称: 高可靠, 沉板CL=-0.87	
X.X	±0.30	X.X*	±3° APPD: 核准: PART NO: 产品编号: DC400170-1092-2H
X.XX	±0.20	X.XX*	±2° CHECK: 校对: 王建业 DATE SCALE UNIT CODE NUMBER
X.XXX	±0.10	X.XXX*	±1° DRAW: 黄艳兰 2016-03-12 1:1 mm A001