


P.C.B LAYOUT  
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)



**PS-22F02XX**  
 PUSH SWITCH  
 G-Switch P/N  
 N=NO LOCK  
 L=LOCK  
 A=黑色  
 B=红色  
 C=蓝色  
 H=黄色  
 D=其它

G-Switch Specification:  
 Operating temperature range: -30°C to +85°C  
 Rating: 50mA, 12V DC  
 Insulation resistance: 100MΩ min, 100V DC  
 Dielectric strength: 250V AC for 1 min  
 Contact resistance: 30mΩ max.  
 Switch Life: 10000 cycles min

		<b>G-Switch Electronic Technology CO., Ltd.</b>	
DESIGN	陈锋枫	DATE	2016.05.29
CHECKED		DATE	
APPROVED		DATE	
<a href="http://www.dg-switch.com">http://www.dg-switch.com</a>		REV:	X1
TEL: 0769-82388879		SCALE:	4:1
		SIZE:	A4
		SHEET:	1/1
		UNIT:	mm

5  
4  
3  
2  
1

A B C D E

5

4

3

2

1