



Pin	A	B	C
2	1.25	7.50	
3	2.50	8.75	
4	3.75	10.00	2.50
5	5.00	11.25	3.75
6	6.25	12.50	5.00
7	7.50	13.75	6.25
8	8.75	15.00	7.50
9	10.00	16.25	8.75
10	11.25	17.50	10.00
11	12.50	18.75	11.25
12	13.75	20.00	12.50
13	15.00	21.25	13.75
14	16.25	22.50	15.00
15	17.50	23.75	16.25
16	18.75	25.00	17.50



技术参数  
 间距: 1.25  
 温度范围: -25~+85°C  
 额定电压: 125V AC, DC  
 额定电流: 1.0A AC, DC  
 接触电阻: 20mΩ  
 绝缘电阻: 100MΩ  
 耐压: 500V AC/minute

线性公差 / General Tolerance		标记		变更内容		签名		年月日	
X	±0.2								
X.X	±0.1								
X.XX	±0.05								
角度公差 / Angle Tolerance									
X°	±5.0°								
X.X°	±3.0°								
X.XX°	±1.0°								
视角 / Projection									
		审核							
		工艺				批准			

材料 / Material  
 ①塑座: LCP 本色  
 ②接触针: 黄铜 (镀锡)  
 ③焊片: 黄铜 (镀锡)



品名 / ProduceName  
**MX1.25 卧贴 6P**  
 型号 / Model  
**ZX-MX1.25-6PWT**

阶段标记  
 版本: 2.0  
 比例: 1:1  
 共 1 张 第 1 张