


SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

| Circuit | Part NO. | Dimensions mm | |
|---------|---------------|---------------|-------|
| | | A | B |
| 2 | HC-5557-2A-X | 4.20 | 9.60 |
| 3 | HC-5557-3A-X | 8.40 | 13.80 |
| 4 | HC-5557-4A-X | 12.60 | 18.00 |
| 5 | HC-5557-5A-X | 16.80 | 22.20 |
| 6 | HC-5557-6A-X | 21.00 | 26.40 |
| 7 | HC-5557-7A-X | 25.20 | 30.60 |
| 8 | HC-5557-8A-X | 29.40 | 34.80 |
| 9 | HC-5557-9A-X | 33.60 | 39.00 |
| 10 | HC-5557-10A-X | 37.80 | 43.20 |
| 11 | HC-5557-11A-X | 42.00 | 47.40 |
| 12 | HC-5557-12A-X | 46.20 | 51.60 |

Ordering Information



| | | | | | | | | | | |
|-----------|------------------------|-------------------|------------------|-------|-------------------|--|--|--------------|--------------|-----|
| | | | GENREL TOLERANCE | | 制 图 DRAWING | | 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD | | | |
| | | | DIM | TOL | 审 核 CHECK | | | | | |
| | | | X. X | ±0.30 | 批 准 APPROVAL | | 产品名称 TITLE | 4.20 单排 直针 | 版本 REV. | A |
| 1 | | | 初版发行 | | 比 例 SCALE | | 产品料号 PART NO. | HC-5557-NA-X | 单 位 UNITS | mm |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | Angle | ±3.0° | 投 影 Projection | | 材 料 MATERIAL | | 页 次 SHEET | 1/1 |