



Figure similar

30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Metal Operator, Round Push-Pull Operator Non-Illuminated Mushroom Head Cap Small 1 3/4" (44.5 mm) Plastic, Black 2 Position Maintained, Pull-to-Release UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

|   |                           |
|---|---------------------------|
| <b>design of the product</b>              | Actuator round            |
| <b>Enclosure</b>                          |                           |
| number of command points                  | 1                         |
| delivery state as a kit                   | No                        |
| <b>Actuator</b>                           |                           |
| color of the actuating element            | black                     |
| material of the actuating element         | plastic                   |
| type of unlocking device                  | pull-to-unlatch mechanism |
| number of switching positions             | 2                         |
| <b>Front ring</b>                         |                           |
| product component front ring              | Yes                       |
| design of the front ring                  | standard                  |
| material of the front ring                | metal                     |
| color of the front ring                   | chrome                    |
| <b>Holder</b>                             |                           |
| material of the holder                    | Metal                     |
| <b>General technical data</b>             |                           |
| product component                         |                           |
| • light source                            | No                        |
| degree of pollution                       | 1                         |
| protection class IP                       | IP66                      |
| <b>Ambient conditions</b>                 |                           |
| ambient temperature                       |                           |
| • during operation                        | -35 ... +70 °C            |
| • during storage                          | -40 ... +85 °C            |
| <b>Installation/ mounting/ dimensions</b> |                           |
| shape of the installation opening         | round                     |
| <b>Certificates/ approvals</b>            |                           |
| <b>Further information</b>                |                           |

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52PP2W1>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52PP2W1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52PP2W1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:52PP2W1&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52PP2W1&lang=en)

---

last modified:

5/31/2021 