



Circuit breaker 10kA, 1-pole, D, 6A according to UL 489-277V

Model	
product brand name	SENTRON
product designation	Miniature circuit breakers
design of the product	Miniature circuit-breaker 5SJ4
General technical data	
number of poles	1
tripping characteristic class	D
mechanical service life (switching cycles) / typical	10 000
installation environment regarding EMC	Suitable for environment B (immunity to interference not applicable)
reference code / according to DIN 40719 extended according to IEC 204-2 / according to IEC 750	F
overvoltage category	3
degree of pollution	3
Voltage	
type of voltage / of the operating voltage	AC/DC
insulation voltage (Ui) / at AC / rated value	440 V
Supply voltage	
supply voltage / at AC / rated value	400 V
operating voltage	
• at AC / according to UL 489 and CSA C22.2 No. 5-02 / maximum	277 V
• at DC / rated value / maximum	60 V
• at DC / single channel / according to UL 489 and CSA C22.2 No. 5-02 / maximum	60 V
• at DC / 2-channel / according to UL 489 and CSA C22.2 No. 5-02 / maximum	125 V
supply voltage frequency / rated value	50 Hz
Protection class	
protection class IP	IP20, with connected conductors, IP 40 in the handle range
Switching capacity	
switching capacity current	
• according to EN 60898 / rated value	10 kA
• according to IEC 60947-2 / rated value	15 kA
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	2.7 W
Current	
operational current	
• at 30 °C / rated value	6 A
• at 40 °C / rated value	6 A

• at 45 °C / rated value • at 50 °C / rated value • at 55 °C / rated value • at 60 °C / rated value • at AC / rated value	5.8 A 5.7 A 5.6 A 5.4 A 6 A
Main circuit	
type of voltage supply / at AC / according to UL 489 and CSA C22.2 No. 5-02	480/277
suitability for operation	Mechanical engineering / industry
Product details	
product component / neutral conductor switching	No
product feature / touch protection	Yes
product component	
• tunnel terminals top • tunnel terminals bottom • combined terminal top • combined terminal bottom	No No Yes Yes
product feature	
• halogen-free • sealable • silicon-free	Yes Yes Yes
product extension / installable / supplementary devices	Yes
Product function	
product function / note	Terminal tightening torque for Cu, 60/75°C; 3.5Nm/31lb.in
Short circuit	
breaking capacity short-circuit current (I _{cn}) / at AC / according to UL 1077 and CSA C22.2 No.235	10 kA
Connections	
connectable conductor cross-section / finely stranded / with core end processing	
• minimum • maximum	0.75 mm ² 25 mm ²
tightening torque / with screw-type terminals / maximum	3.5 N·m
position / of power supply cord	Any
Mechanical Design	
height	121 mm
width	18 mm
depth	70 mm
installation depth	70 mm
number of modular width units	1
fastening method	on standard mounting rail
mounting position	any
net weight	175 g
Environmental conditions	
vibration resistance	50 m/s ² at 25 to 150Hz and 60m/s ² at 35Hz (4sec)
ambient temperature / during operation	
• minimum • maximum	55 °C -25 °C
ambient temperature / during storage	
• minimum • maximum	-40 °C 75 °C
Certificates	
reference code	
• according to EN 61346-2 • according to IEC 81346-2	F F
General Product Approval	
Declaration of Conformity	

[Confirmation](#)



Declaration of Conformity	Test Certificates	other
------------------------------	-------------------	-------



[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SJ4106-8HG42>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SJ4106-8HG42>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ4106-8HG42

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



