

30mm BlackMax, Epoxy Coated Corrosion Resistant Complete Metal Unit Illuminated Push-Pull Operator Transformer type, 600V AC LED Lamp Mushroom Head Cap Small 1 3/4" (44.5 mm) Plastic, Green 3 Position Momentary 1 N.C.+1 N.C. Extra Late Break Heavy Duty Contacts, A600/P600 UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)
<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com>

