

	Manual Motor Control, Manual Switch,
product brand name	MMS
design of the product	Manual Switch
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 115 V rated value	2 hp
Mounting/wiring	
fastening method	wall mounting
type of electrical connection for supply voltage line-side	Screw-type terminals
Certificates/ approvals	
certificate of suitability	UL
Further information	
Industrial Controls - Product Overview (Catalogs, Brochures,...)	
www.usa.siemens.com/iccatalog	
Industry Mall (Online ordering system)	
https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MMSKG11A	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
https://support.industry.siemens.com/cs/US/en/ps/US2:MMSKG11A	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:MMSKG11A&lang=en	
Certificates/approvals	
https://support.industry.siemens.com/cs/US/en/ps/US2:MMSKG11A/certificate	

last modified:

5/31/2021 