




RoHS



P.C.B Layout (Pattern side)

规格说明: Specifications

电气特性: Electrical

1. 额定电流: Current Rating  
1.5A/contact terminal
  2. 额定电压: Voltage Rating  
30V DC
  3. 接触阻抗: Contact Resistance  
50 milliohms Max
  4. 耐电压: Dielectric Withstanding Voltage  
AC 500V/1MINUTE.
  5. 绝缘阻抗: Insulation Resistance  
1000MEGA Ohms Min
- 物理性能: Mechanical
1. 插拔力: Connector Mate and Unmate Force  
Insertion force: 35N(3.57kgf) MAX  
Extraction force: 10-35N(1.02-3.57kgf) Min
- 端子保持力: Terminal Retention  
1.0kgf(MIN)
- 耐久性: Durability  
3000cycles. EXTRACTLON FORCE:  
10-35N(1.02-3.57kgf)

|     |          |        |     |           |             |
|-----|----------|--------|-----|-----------|-------------|
| ③   | Terminal |        | 4   | Brass     | Ag Plating  |
| ②   | Shell    |        | 1   | SPCC      | Ni Plating  |
| ①   | Base     |        | 1   | PBT+30%GF | White/Black |
| NO. | Name     | Number | Qty | Materil   | Remarks     |

YUANDI® Yuandi Electronics Co, Ltd

|          |      |       |                |
|----------|------|-------|----------------|
| design   | date | name  | USB CONNECTOR  |
| Review   | date | model | USB180-01-T1-W |
| Approved | date |       |                |

Drawing number: 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number A4