





REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASED	18. 04. 09	DENGJUN. TAN
A1	统一料号	18. 11. 28	Mark



- 技术要求:
- 电气特性: 特性阻抗: 50Ω; 适用频率范围: DC-6GHz; 驻波比: 最大1.50; 插入损耗: 最大-15dB。
测试方法: 双头MHF-1-PLUG电缆组件, 外露长度为100mm, 使用矢量网络分析仪测试。
 - 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目
 - 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
 - 包装规范: 200PCS/扎, 5扎/包, 即1000PCS/包。
 - 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

3	2SBKR0200	黑帽子, OD3.50*L13.00, 内径2.2	1	---
2	2TA020BK1-103	热缩管, OD2.0*L103.00 黑色无收缩比例为2:1	1	---
1	2C5R17811BN1	微细同轴电缆, RG178, 银锡线, 棕色	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS

GENERAL TOLERANCE: LINEAR: X ±0.20 X.X ±0.15 X.XX ±0.05 X.XXX ±0.01 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司			
FILE NAME: 产品图		TITLE: 射频电缆组件			
ENG/DATE: DENGJUN. TAN/18. 04. 09		RF CABLE,RG178透明棕银锡线,P1端剥皮镀锡; P2端套硅胶帽,裁线长L=110mm			
CHE/DATE:		P/N: 3C0618Q01-001			
APP/DATE:		UNIT: mm		SCALE: 1:1	REVISION: A0
					SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS

*NO USING ESTRICTED AND BANNED SUBSTANCE

H340