



RoHS



P.C.B Layout (Pattern side)

规格说明: Specifications

电气特性: Electrical

- 额定电流: Current Rating
1.5A/contact terminal
 - 额定电压: Voltage Rating
30V DC
 - 接触阻抗: Contact Resistance
50 milliohms Max
 - 耐电压: Dielectric Withstanding Voltage
AC 500V/1MINUTE.
 - 绝缘阻抗: Insulation Resistance
1000MEGA Ohms Min
- 物理性能: Mechanical
- 插拔力: Connector Mate and Unmate Force
Insertion force: 35N(3.57kgf) MAX
Extraction force: 10-35N(1.02-3.57kgf) Min
- 端子保持力: Terminal Retention
1.0kgf (MIN)
- 耐久性: Durability
3000cycles. EXTRACTLON FORCE:
10-35N(1.02-3.57kgf)

(C)	Terminal		4	Brass	Ag Plating
(B)	Shell		1	Brass	Ni Plating
(A)	Base		1	PBT	White
NO.	Name	Number	Qty	Material	Remarks

YUANDI® Yuandi Electronics Co., Ltd

design	date	name	USB CONNECTOR
Review	date	model	USB90-10-T2-W
Approved	date		

Drawing number: Proportion 1:1 unit mm gaps number A4

modify Review Approved Tolerance not specified