



Pin length		Shell foot length	
CODE	P	CODE	G
P3	1.50	G3	1.50
P4	2.00	G4	2.00



电气特性:Electrical

- 1.额定电流:Current Rating
1.0A/contact terminal
 - 2.额定电压:Voltage Rating
30V DC
 - 3.接触阻抗>Contact Resistance
50 milliohms Max
 - 4.耐电压:Dielectnic Withstanding Voitage
AC 100V/1MINUTE.
 - 5.绝缘阻抗:Insulation Resistance
100MEGA Ohms Min
- 物理性能:Mechanical
- 1.插拔力:Connector Mate and Unmate Force
Insertion force:3.57kgf(MAX)
Extraction force:1.02kgf(Min).0.81~2.05kgf(Min).
- 端子保持力:Terminal Retention
0.5kgf(MIN)

③	Terminal		5	Brass	Au Plating
②	Shee		1	SUS	Nickel Plating
①	Base		1	LCP	Black
NO.	Name	Number	Qty	Matril	Remarks

YUANDI® Yuandi Electronics Co,Ltd

design	date	name	USB CONNECTOR
Review	date		
Approved	date		
number:		model	MICRO-05-G□P□-T3

Recommended P.C.B Layout

							angle	±2°		design		date		name	USB CONNECTOR			
							10~30	±0.30		Review		date						
							5~10	±0.20		Approved		date						
							~ 5	±0.10		Drawing number:								model
					modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number				A4	