








高推柄 High handle



平推柄 short handle



电路图



PART NO.	A	B
DA-01-x	3.54	
DA-02-x	6.64	2.54
DA-03-x	9.18	5.08
DA-04-x	11.72	7.62
DA-05-x	14.26	10.16
DA-06-x	16.80	12.70
DA-07-x	19.34	15.24
DA-08-x	21.88	17.78
DA-09-x	24.42	20.32
DA-10-x	26.96	22.86
DA-11-x	29.50	25.40
DA-12-x	32.04	27.94

开关特性：

- 1、电流规格：切换时：25mA@24VDC
- 2、接触电阻：50M Max
- 3、绝缘电阻：100M @250VDC
- 4、绝缘强度：500VAC/1min
- 5、操作力度：1000gf Max
- 6、电气寿命：2000次
- 7、适用温度：-20 to 80 (无结冰)
- 8、焊接要求：
手工焊接：320 不超过2秒 (30瓦烙铁max.)
波峰焊：260 不超过5秒
在焊接和清洁过程中开关处于断开状态
- 9、开关出厂处于断开状态

材料：

盖子：PBT塑料（红色或蓝色）
底座：PBT塑料（黑色）
操作杆：PBT塑料（白色）
灌封胶：环氧树脂
端子：镀锡磷青铜，触点镀金3μ"（或整体镀金1μ"）
电镀：(全金/半锡金)

modify	Review	Approved	angle	±2°	10~30	±0.30	5~10	±0.20	~ 5	±0.10	design	date	name	DA-03-B	
											Review	date	name		
											Approved	date	name		
											Drawing number:				
											Proportion	1:1	unit	mm gape number	A4