


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2010.06.08	謝金發
02	△	依上級要求變更圖號	2012.04.25	李芳忠
03	△	依業務要求增加82電鍍碼	2019.10.17	馮國東

Specifications
 Current Rating: 2.0Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials

Contact Material: Phosphor Bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.




Ordering Information

C SFA201 - XX XX A 001 R 1 A X

No. of Pins per Row: 02~40
 Standard Plating: 02=Gold Flash
 Selective Plating: 01=Tin
 05=Gold Flash/Tin
 △82=1u" gold over 100~150u" Nickel

Color: 1=Black
 Standard Packing: A=Box, C=Tube, E=Cap+Tube, F=Cap+Tape&Reel



Recommended P.C.Board Layout

格菱股份有限公司 Greenconn Corporation			GENERAL TOLERANCE X. ±5.0° X. ±3.0° .XX ±2.0° .XXX ±1.0°		DESIGNED: 馮國東 CHECKED: 邱國廷(代) CO SIGNED: 鍾隆達 APPROVED: 邱國廷		DWG. NO. CSFA201-CA1RA		TITLE: 2.00 FEMALE HEADER DUAL ROWS DIP TYPE CONNECTOR		
REV. 03	UNIT. mm	SCALE. 5:1	PAGE. 1/1	X. ±5.0° X. ±3.0° .XX ±2.0° .XXX ±1.0°		DATE: 2019.10.17 DATE: 2019.10.17 DATE: 2019.10.17 DATE: 2019.10.17		PART NO. CSFA201-XXXX A001R1AX			

